



	(Left)	(Right)
Column	: Shodex IEC DEAE-825 (8.0mmID*75mm)	: Shodex IEC DEAE-420N (4.6mmID*35mm)
Eluent	: (A); 20mM Tris-HCl buffer(pH7.0) (B); (A) + 0.5M NaCl Linear gradient: 0min to 60min, (A) to (B)	: (A); 25mM Tris-HCl buffer(pH8.0) (B); (A) + 0.5M NaCl Linear gradient: 0min to 10min, (A) to (B)
Flow rate	: 1.0mL/min	: 1.5mL/min
Detector	: Shodex UV(280nm)	: UV(280nm)
Column temp.	: Room temp.	: Room temp.